

Skin Contact Applications - Electrodes & Wearables

Hydrogel-Free Bio-Signal Sensing Transfer Tape

FLEXcon® OMNI-WAVE™ bio-signal sensing transfer tape adhesive has been tested for ISO 10993-10 biocompatibility (irritation, sensitization) by an independent testing agency specializing in biocompatibility. The adhesive also meets the requirements of AAMI/ANSI EC-12.

FLEXcon® OMNI-WAVE™ hydrogel-free adhesive applications include:

- *Electrodes (diagnostic & therapeutic)*
- *Sensors for wearable devices*

We have the flexibility to customize constructions to meet your converting and end-use requirements. This includes release liner, carrier film, adhesive thickness, and other variables.

For more information on FLEXcon's pressure-sensitive film solutions for skin contact applications, contact your local Sales Representative or our Performance Products Business Team at (508) 885-8440.

Product ID #: FLX068983



Product:

**FLEXcon® OMNI-WAVE™
TT 200 Black H-502
150 Poly H-9 44PP-8**

Benefits:

- H-502 hydrogel-free skin contact adhesive (transfer tape) engineered for short-term wear (3 days) for medical device attachment (electrodes or sensors) demonstrates minimal skin irritation as compared to hydrogel electrodes
- Conductive adhesive layer allows electronics to send and receive waveform signals between the surfaces it connects to
- Product performance is not affected by humidity
- 1.5 mil ultra-smooth polyester release liner provides ultimate smoothness and flow-out of adhesive, and is ideal for roll-form converting
- 44 lb. polycoated natural Kraft release liner ideal for roll-form converting
- Patented FLEXcon® OMNI-WAVE™ technology
- Association for Advancement of Medical Instrumentation (AAMI) compliant
- Passes ISO 10993-10 (biological evaluation of medical devices) for sensitization and irritation



FLEXcon® OMNI-WAVE™

TT 200 Black H-502

150 Poly H-9 44PP-8

PRODUCT DATA	VALUE		TEST METHOD
Physical Properties			
Thickness (Mils[microns])	44 PP-8 Liner	3.0 (76) +/- 10%	ASTM D 3652 (Modified for use with non-tape products)
	Adhesive	2.0-2.2 (51-56) +/- 0.1 (3)	
	150 Poly H-9 Liner	1.4 (36) +/- 5%	
Adhesion Properties			
Ultimate Peel from	Average		ASTM D 3654 Method A a. 1 hr. dwell b. 1 sq. in. surface c. 4 lb. load
	Oz/In	(N/m)	
Stainless Steel	13	(143)	
Expected Shear			
Room Temp (hours)	2		
Tack (gm/sq cm)	340		ASTM D 2979
Electrical Properties			
Z-Direction Resistance	Less than 20 Ohms/in ²		ASTM D 257
Surface Resistivity	Less than 200 Ohms/square		ASTM D 257
Storage Stability	Two years stored at 70°F (21°C) and 50% RH in the original packaging; two year out-of-package shelf life		

Adhesion Properties - Ultimate Peel from test method: ASTM D 903 (15 min. dwell)
a. 180° degree peel

DISCLAIMER: FLEXcon MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO ANY IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, COURSE OF PERFORMANCE, OR TRADE USAGE. This product is a device component intended solely for further processing, manufacturing, incorporation into a finished device, and is further intended only for use as a device component on intact skin (i.e., not intended for use in the presence of open sores or wounds nor for applications inside the body). Customer is solely responsible for determining whether this component product is fit for Customer's intended use, including, without limitation, incorporation into Customer's finished device(s), and for performing any additional testing that may be necessary to support Customer's intended use. Customer is solely responsible for ensuring that its use of the component product is in compliance with the applicable laws and for obtaining any necessary clearances or approvals from its use of the component product and any finished device that incorporates the component product. Full biocompatibility results are available upon request.

Product Performance and Suitability

All of the descriptive information, the typical performance data, and recommendations for the use of FLEXcon products shall be used only as a guide and do not reflect the specification or specification range for any particular property of the product. Furnishing such information is merely an attempt to assist you after you have indicated your contemplated use and shall in no event constitute a warranty of any kind by FLEXcon. All purchasers of FLEXcon products shall be responsible for independently determining the suitability of the material for the purpose for which it is purchased. No distributor, salesman, or representative of FLEXcon is authorized to give any warranty, guaranty, or make any representation in addition or contrary to the above.

Last Modified On: 01/27/2023

